

## 1PLD7504HD

by Burndy  
Catalog ID: 1PLD7504HD

Prop 65 Notice

UV Rated Black UNITAP



## Product Details

### General

Hex Key	3/8 in
Installation Torque Recommended in-lb	500 in-lb
Number Of Ports	4
Temperature Rating	-40°C to 135°C
Trade Name	UNITAP™
UPC	621945480742

### Dimensions

Dimension - L Length Overall mm	136.652
Dimension - Length Overall inch	5.38

### Electrical Ratings

Rating - Minimum Voltage	600 V
--------------------------	-------

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)