



1PLD7508

by Burndy
Catalog ID: 1PLD7508

Prop 65 Notice

UV Black Plastisol Covered Al Distribution Connectors, Double Sided Entry, 8 Ports, #2 AWG- 750 Kcmil, 600 V, 3/8" Hex

Product Details

General

Hex Key	3/8
Installation Torque Recommended in-lb	500 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	8
Physical Attribute - Number of Screws	8
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
UPC	781810287453
UPC 12 Digit	7818102874533

Dimensions

Dimension - Height fraction	3 in
Dimension - Height inch	3.00 in
Dimension - L Length Overall mm	283 mm
Dimension - Length Overall inch	11.13 in
Dimension - Screw Size inch	13/16
Dimension - Width inch	3.38 in
Dimension - Width mm	86 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	2 AWG-750 kcmil

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	2 AWG-750 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)