


1PLM2/012

by Burndy
Catalog ID: 1PLM2/012

Mounted Block Tap Connector, 12 Ports, Single Side Entry, 9.33 IN L



Product Details

General

Installation Torque Recommended in-lb	275 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	12
Physical Attribute - Number of Screws	14
Plated	Y
Plating Type	Clear Plated
Temperature Rating	194° F
Trade Name	UNITAP™
UPC	781810307854
UPC 12 Digit	7818103078544

Dimensions

Dimension - Height fraction	1-1/2 in
Dimension - Height inch	1.50 in
Dimension - L Length Overall mm	237 mm
Dimension - Length Overall inch	9.33 in
Dimension - Width inch	1.44
Dimension - Width mm	36 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - AL Str Size Range	14 AWG-2/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	14 AWG-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)