

38X125HEBBOX

by Burndy
Catalog ID: 38X125HEBBOX

Prop 65 Notice

Silicon Bronze Bolt, 1.25 in L, Hexagonal bolts, Thread size: 3/8-16.

Features: Thread Size: 3/8-16, Stud Length: 1-1/4 IN, Package: Box



Product Details

General

Application	<ul style="list-style-type: none"> • Grounding • Distribution • Substation • Transmission
Connector Type	Bolt - Hex
Installation Torque Recommended in-lb	240 LBS/in
Material	Bronze, Silicon (DURIUM is a trademark)
Sub Brand	HARDWARE BOLT, DURIUM
Trade Name	DURIUM™
Type	HEB, Hexagonal Bolts
UPC	781810011737
UPC 12 Digit	7818100117377

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Length Overall inch	1.25 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)