



AYPO600

by Burndy
Catalog ID: AYPO600

Prop 65 Notice

Aluminum Compression Pin Adapter, 600 kcmil, 0.73" Plug Dia, 1.64" Plug length, Al/Cu Rated, Tin Plated.

Features: All-Aluminum Electro-Tin Plated Design: Eliminates Possible Bi-Metallic Corrosion And Provides The Shortest Connector Length Design Possible, Shortest Connector Length Design Possible: Permits Easy Installation In Equipment With Limited Working Space, Solid Electro-Tin Plated Aluminum Plug: Proper Electrical Connection Made Easily, Eliminates How Tight Is Tight Problem, Smooth Surface On The Solid EC Aluminum Electro-Tin Plated Plug: Provides Greater Area Contact Establishing Excellent Electrical Conductivity, Solid Plug Has Equivalent Cross-Sectional Area As Current Carrying Equivalent Copper Wire: Permits Use Of Larger Aluminum Wire To Connect Equipment, Offset Plug Design Available In Sizes 2/0 AWG Through 750 KCMIL: Provides Flexibility And Maximizes The Use Of Limited Space Eliminating Interference Between Conductors And Equipment, Electro-Tin Plated: Resists Corrosion, Factory Prefilled With The Proper Amount Of PENETROX Joint Compound: PENETROX, BURNDYs Oxide Inhibiting Compound With Conductive Metallic Particles Penetrates Aluminum Oxide Between Strands And Forms An Air-Tight Connection, EPDM Rubber Covers Are Supplied With Each Connector And Are Rated For 600 V: Eliminates Taping, Only (5) Die Sets Install The Complete Line From #6 To 750 KCMIL: Lowers Inventory Requirements And Saves Money, Supplied In A Plastic Convenience Pack: The Cover And Connector Are Kept Together And Free Of Foreign Material Until Used, Connectors Are Clearly Marked With Catalog Number, Wire Size, And Color Coded Die Index: Provides Clear, Easy To Use Information To Lower Installed Cost, Plug/pin Length: 1.64 IN, Color Code: Yellow, Offset Pin: Yes, Cover Length: 46 IN, Dieless Tools (number Of Crimps): HYTOOL: Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (3), Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y39, Y750 Tool, U39ART-2 Die, (3), Y46 Tool, U39ART-2 Die With PUADP-1 Adapter, (3), Die Index: 936 Element A, Plug/pin Diameter: 0.73 IN, Wire Strip Length: 1-3/4 IN

Product Details

General

Application	For Aluminum And Copper Conductors, Mechanical Connectors In Molded Case Circuit Breakers, Panel Board Equipment And Meter Sockets
Color Code	Yellow
Connector Type	Pin adapter
Die Index	936
Insulation	Y
Insulation Type	Rubber
Material	Aluminum
Physical Attribute - Number of Crimps Required	3
Pin Type	Offset
Plated	Y
Plating Type	Tin
Sub Brand	HYPLUG
Temperature Rating	194

Trade Name	HYPLUG™
Type	Aluminum Pin Adapters
UPC	781810738504
UPC 12 Digit	7818107385044

Dimensions

Dimension - A Outside Diameter inch	1.46 in
Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.59 in
Dimension - B Outside Diameter inch	0.73 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.02 in
Dimension - P inch	1.64 in
Dimension - Strip Length inch	1-3/4 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000 V

Conductor Related

Conductor - AL Str Size	600 kcmil
Conductor - Copper DLO Size	444 (1100/#24) DLO
Conductor - Copper Flex I Size	-
Conductor - Copper Str Size	600 kcmil
Conductor Type	CU C DLO-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)