



B1310

by Burndy
Catalog ID: B1310

BURNDYWELD, BCC-6, Features: Molds are used to join horizontal parallel tap to run connections. The tap cable is over the run cable. Size range is #6 through 4/0 solid or concentric stranded copper conductors, For Horizontal Parallel Tap.

Features: BCC-6 Type Molds Are Used To Join Horizontal Parallel Tap To Run Connections; The Tap Cable Is Over The Run Cable; Conductor Type: Concentric Stranded Copper; Includes: Handle; Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp; Required Tools: B38-0309-00 Flint Ignitor; Cartridge Type: Standard

Product Details

General

Application	To Join Horizontal Parallel Tap To Run Connections
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Type	Molds
UPC	781810382462
UPC 12 Digit	7818103824622

Conductor Related

Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Str Run	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Solid-Tap

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)