



BA200

by Burndy
Catalog ID: BA200

Shim Stock and Adapter Sleeves

Product Details

General

| | |
|--------------|---------------------|
| Trade Name | BURNDYWeld® |
| Type | Tools & Accessories |
| UPC | 781810405123 |
| UPC 12 Digit | 7818104051233 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - Inside Diameter inch | 0.111 in |
| Dimension - Length Overall inch | 1 in |
| Dimension - Outside Diameter inch | 0.156 in |

Conductor Related

| | |
|-------------------------------|---------------------------|
| Conductor - Copper Solid Size | #10 AWG, #12 AWG, #14 AWG |
| Conductor - Copper Str Size | #12 AWG, #14 AWG |
| Conductor - Rod Size | #6 AWG STR & Sol |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)