



BB024L6T14

by Burndy
Catalog ID: BB024L6T14

Prop 65 Notice

Flexible Copper Braid, 6.00 in L, Flexible copper braid jumpers designed to take up linear expansion and contraction

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
UPC	781810552520
UPC 12 Digit	7818105525200

Dimensions

Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Dimension - N inch	0.5 in
Dimension - Stud Size inch	1/4

Electrical Ratings

Rating - Indoor Amperage	93
Rating - Outdoor Amperage	93

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)