



## BC28

by Burndy  
Catalog ID: BC28

Prop 65 Notice

For Guy Wire, 2/0 Str - 4/0 Str.

## Product Details

### General

Connector Type	Deadend
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013496

### Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.63 in
Dimension - Height fraction	2-3/8 in
Dimension - Height inch	2.375 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Pad Width inch	1.13 in
Dimension - Pin Diameter fraction	1/2 in
Dimension - Pin Diameter inch	0.50 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

### Conductor Related

Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2/0 AWG-4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

## Logistics

Minimum Pack Quantity	10
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)