



BDBCOVER1

by Burndy
Catalog ID: BDBCOVER1

Prop 65 Notice

POWER DISTRIBUTION BLOCKS.

Product Details

General

Material	Polycarbonate
Number Of Poles	2
Plated	N
Plating Type	Unplated
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810115336
UPC 12 Digit	7818101153366

Dimensions

Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.36 in
Dimension - Width inch	2.90 in
Dimension - Width mm	74 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)