



## BDBLCS4K3FS

by Burndy  
Catalog ID: BDBLCS4K3FS

Prop 65 Notice

POWER DISTRIBUTION BLOCKS.

## Product Details

### General

Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810676882
UPC 12 Digit	7818106768822

### Dimensions

Dimension - Height inch	4.15
Dimension - L Length Overall mm	231
Dimension - Length Overall inch	9.09

### Electrical Ratings

Amperage Rating	620 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

### Conductor Related

Conductor - AL Str Run Range	6 AWG - 350 kcmil
Conductor - AL Str Tap Range	14 AWG - 2/0 AWG
Conductor - Copper Str Run Range	6 AWG - 350 kcmil
Conductor - Copper Str Tap Range	14 AWG - 2/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - cULus	Yes

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

1
---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)