



BDBLHCCOVER

Catalog ID: BDBLHCCOVER

Prop 65 Notice

Power Distribution Block Safety Cover.

Provided capability to create as many poles as required, Up to 30 tap conductor accommodated $\,$

Product Details

General

Application	Industrial control feeder, HVAC system and wire ways
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Туре	BDB
UPC	781810646120
UPC 12 Digit	7818106461200

Dimensions

Dimension - Height inch	0.87 in
Dimension - L Length Overall mm	154 mm
Dimension - Length Overall inch	6.07 in
Dimension - Pad Width inch	2.61 in
Dimension - Width inch	2.61 in
Dimension - Width mm	66 mm

Electrical Ratings

Rating - M	inimum Voltage	600

Conductor Related

Conductor Type	AL C Str-Run
	CU C Str-Run
	AL C Str-Tap
	• CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)