



BDBMCS2F1FS

by Burndy
Catalog ID: BDBMCS2F1FS

Prop 65 Notice

Distribution block, One pole Finger Safe 14-2/0 AWG (Run), 14-2 AWG (Tap), Hole layout- 2(Run)/6(Tap).

Provides capability to create as many poles as required and Up to 30 tap conductors accommodated,Finger-Safe style

Product Details

General

Application	VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676363
UPC 12 Digit	7818106763633

Dimensions

Height	4.52 in
Length	5.71 in

Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor Type	- AL C Str-Run - CU C Str-Run - AL C Str-Tap - CU C Str-Tap
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)