



BDBMHC145003

by Burndy
Catalog ID: BDBMHC145003

Prop 65 Notice

Terminal block covers, AWG 4 - 500 kcmil (Run), AWG 14 - 2/0 (Tap),
Power Distribution Block.

Provided capability to create as many poles as required, Up to 30 tap
conductor accommodated

Product Details

General

Application	Industrial control feeder, HVAC system and wire ways
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810645772
UPC 12 Digit	7818106457722

Dimensions

Dimension - Height inch	3.25 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	5.28 in
Dimension - Width mm	134 mm

Electrical Ratings

Amperage Rating	380 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	4;3;2;1;0;2/0;3/0;4/0;250;266.8;300;336.4;350;397.5;400;450;477;500
Conductor - AL Str Run Range	4-500
Conductor - AL Str Tap	12;10;8;6;4;3;2;1;0;2/0
Conductor - AL Str Tap Range	12-2/0
Conductor - Copper Str Run	4;3;2;1;0;2/0;3/0;4/0;250;300;350;400;450;500
Conductor - Copper Str Run Range	4-500
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2;1;0;2/0

Conductor - Copper Str Tap Range	14-2/0
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)