



BURNDY Catalog Number
UPC Number
Description
Status

BDBMHC162/01
7818106457899
2/0-12-1P-4-14 SEC
Active

Web Use
BURNDY Product Line

Dimensional

Width (in) 1.85
Length (in) 5.00
Height (in) 3.25
Height (mm) 82.6
Length (mm) 127
Width (mm) 47

General

Description ALUM SS PDB'S - BDB
Terminal block covers, AWG 14 -
2/0 (Run), AWG 14 - 2 (Tap),
Product Description Power Distribution
Block, Recommended
torque: 120(Run), 50(Tap)

Conductor(s)

Aluminum Run Size (Range) 12-2/0
Copper Tap Range 14-2
Copper Stranded Run (Range) 14-2/0
Aluminum Tap Size (Range) 12-2

Physical

Type of Plating Tin
Number of Poles 1
Plated (Yes or No) Y
Product Material Aluminum

Approvals / Certifications

UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175