



BDBMHCCOVER

by Burndy
Catalog ID: BDBMHCCOVER

Prop 65 Notice

POWER DISTRIBUTION BLOCKS.

Product Details

General

Insulation	Y
Material	Polycarbonate
Plated	Y
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	781810646137
UPC 12 Digit	7818106461377

Dimensions

Dimension - Height inch	0.65 in
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.37 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)