

BDBSCS1P3

by Burndy
Catalog ID: BDBSCS1P3

Prop 65 Notice

Distribution block, Three pole Open Style 14-2/0 AWG (Run), 14-2/0 (Tap).

Provides capability to create as many poles as required and Up to 30 tap conductors accommodated



Product Details

General

| | |
|--------------------|--|
| Application | VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications. |
| Insulation | Y |
| Material | Aluminum |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | VERSIPOLE |
| Temperature Rating | 194 |
| Trade Name | VERSIPOLE™ |
| Type | BDB |
| UPC | 781810676332 |
| UPC 12 Digit | 7818106763322 |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 600 V |

Conductor Related

| | |
|----------------|--|
| Conductor Type | <ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap |
|----------------|--|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - cULus | Yes |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)