



# **BE12**

by Burndy Catalog ID: BE12

Prop 65 Notice

Copper Braid, 12" Long, 1 Braid, 2 Holes 2 Ferrules, 7/16" Stud, 1-1/2" Stud Hole Spacing, 340 amps Indoor, 405 amps Outdoor.

Made of flat extra flexible, tinned, pure copper braid, with unplated, seamless, pure copper ferrules formed into a rectangular shape on each end.

# **Product Details**

## General

Application	Flexible copper braid jumpers designed to take up linear expansion and contraction
Connector Type	Braid
Material	Copper
Material - Ferrules	Υ
Physical Attribute - Number of Braids	1
Plated	Y
Sub Brand	BRAID
Туре	B, Flexible
UPC	781810807019
UPC 12 Digit	7818108070199

## Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.50 in

# **Electrical Ratings**

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

# Certifications and Compliance

Certification - CSA Approved	Yes

Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

# For further technical assistance, please contact us

## **BURNDY Headquarters**

47 East Industrial Park Drive Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)