



BE24N

by Burndy
Catalog ID: BE24N

Prop 65 Notice

Flexible Cu Braid Jumper, 2 Holes 2 Ferrules, 1.75" Spacing, 24" L, 340 Amps Indoor, 405 Amps Outdoor.

Features: Flexible Braid Jumper, Dimension T: 0.17 IN, Length: 24 IN, Width: 1-1/2 IN, Number Of Braids (ferrule): 1

Product Details

General

Application	For Use On: Designed to take up linear expansion and contraction, compensate for misalignment and absorb vibratory movement of electrical equipment and devices
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Sub Brand	BRAID JUMPER
Type	B, Flexible
UPC	781810005248
UPC 12 Digit	7818100052488

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	9144 mm
Dimension - Length Overall inch	360 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)