



BIBD2/012

by Burndy
Catalog ID: BIBD2/012

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 12 Port, 2 Sided Entry,
14-2/0 Awg, Al/Cu Rated

Product Details

General

| | |
|---------------------------------------|---------------|
| Hex Key | 3/16 |
| Insulation | Y |
| Insulation Type | Plastisol |
| Material | Aluminum |
| Material - Hardware | Aluminum |
| Number Of Ports | 12 |
| Physical Attribute - Number of Screws | 12 |
| Physical Attribute - Screw Type | Allen |
| Physical Attribute - Socket Size | 0.19 |
| Plated | N |
| Plating Type | Unplated |
| Temperature Rating | 194 |
| Trade Name | UNITAP™ |
| UPC | 781810232736 |
| UPC 12 Digit | 7818102327366 |

Dimensions

| | |
|---------------------------------|------------|
| Dimension - Height fraction | 1.375 in |
| Dimension - Height inch | 1.38 in |
| Dimension - L Length Overall mm | 209 mm |
| Dimension - Length Overall inch | 8.24 in |
| Dimension - Width fraction | 1-14/25 in |
| Dimension - Width inch | 1.56 in |
| Dimension - Width mm | 40 mm |

Electrical Ratings

| | |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Conductor Related

| | |
|-------------------------------|---|
| Conductor - AL Str Size | 8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG |
| Conductor - AL Str Size Range | 8 AWG-2/0 AWG |

| | |
|-----------------------------------|--|
| Conductor - Copper Str Size | 14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 Str |
| Conductor - Copper Str Size Range | 14 AWG-2/0 Str |
| Conductor Type | <ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size |

Certifications and Compliance

| | |
|---|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)