



**BURNDY Catalog Number** BIBD2/08  
**UPC Number** 7818102239877  
**Description** 2/0-14 TWO SIDED UNITAP  
**Status** Active

**Web Use**  
 BURNDY Product Line

	<b>Dimensional</b>
Width (in)	1.56
Hex Size (Key)	3/16
Length (in)	5.55
Height (in)	1.38
Height (mm)	35.1
Length (mm)	141
Width (mm)	40
	<b>Electrical</b>
Min Voltage Rating	600
	<b>General</b>
Number of Ports	8
Number of Screws	8
Product Description	Aluminum Multiple Tap Connector, Clear Insulated, 8 Port, 2 Sided Entry, 14-2/0 AWG, Al/Cu Rated
	<b>Conductor(s)</b>
Aluminum Size (Range)	8 AWG-2/0 AWG
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	14 AWG-2/0 Str
	<b>Physical</b>
Type of Hardware	Aluminum
Type of Plating	Unplated
Insulation Type	Plastisol
Plated (Yes or No)	N
Product Material	Aluminum
	<b>Approvals / Certifications</b>
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
<b>Documentation</b>	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175

