



BIBD3504FX

by Burndy
Catalog ID: BIBD3504FX

Prop 65 Notice

MULTI-PORT Double-Sided Entry.

Product Details

General

Insulation	Y
Material	Aluminum
Number Of Ports	4
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945438668
UPC 12 Digit	6219454386688

Dimensions

Dimension - Length Overall inch	3.790 in
---------------------------------	----------

Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Size Range	10AWG-250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)