



## BIBD46

by Burndy  
Catalog ID: BIBD46

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 6 Port, 2 Sided Entry, 14-4 AWG, Al/Cu Rated.

Clear Plastisol covered AL6061-T6 aluminum body, Clear Plastisol

## Product Details

### General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Hex Key	1/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	6
Physical Attribute - Number of Screws	6
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	781810223871
UPC 12 Digit	7818102238711

### Dimensions

Dimension - Height fraction	1.25 in
Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	72 mm
Dimension - Length Overall inch	2.83 in
Dimension - Screw Size inch	1/4
Dimension - Width fraction	1-1/2 in
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 Str
Conductor - Copper Str Size Range	14 AWG-4 Str
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)