



BIBS2/03FX

by Burndy
Catalog ID: BIBS2/03FX

Prop65

UNITAP, Single Sided Entry, #14-#4 Class B & C, #14-#6 Class G,H,I,K, DLO, Aluminum.

Features: Clear Plastisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

Product Details

General

| | |
|--------------------|---|
| Application | Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors |
| Color Code | Black |
| Insulation | Y |
| Material | Aluminum |
| Number Of Ports | 3 |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | UNITAP |
| Temperature Rating | -40° C to 135 °C |
| Trade Name | UNITAP™ |
| Type | BIBS, Multi-Port |
| UPC | 621945439313 |
| UPC 12 Digit | 6219454393133 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - Length Overall inch | 1.938 in |
|---------------------------------|----------|

Electrical Ratings

| | |
|--------------------------|-------|
| Amperage Rating | 175 A |
| Rating - Minimum Voltage | 600 |

Conductor Related

| | |
|-------------------------------|--|
| Conductor - AL Str Size Range | 1 AWG-14 AWG |
| Conductor Type | <ul style="list-style-type: none"> AL C Str-Size CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|-------------|
| Certification - CSA Approved | No |
| Industry Standard(s) | UL468A-468B |
| Standards - Industry Standards Met | UL468A-468B |
| Standards - RoHS Compliance Status | CM |

| | |
|-----------|-----|
| UL Listed | Yes |
|-----------|-----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)