



## BIBS3504DB

by Burndy  
Catalog ID: BIBS3504DB

Prop 65 Notice

Direct Burial Unitap, 350 Kcmil -12 AWG Str., 5.03 in L, Designed specifically for direct burial applications.

Dual rated for aluminum or copper conductors, Each unit is individually marked for ease of identification

## Product Details

### General

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Application                           | For Outside Direct Burial        |
| Installation Torque Recommended in-lb | 450 LBS/in                       |
| Insulation                            | Y                                |
| Material                              | Aluminum                         |
| Number Of Ports                       | 4                                |
| Plated                                | N                                |
| Plating Type                          | Unplated                         |
| Sub Brand                             | UNITAP                           |
| Temperature Rating                    | 194                              |
| Trade Name                            | UNITAP™                          |
| Type                                  | BIBS, Multi-Port - Direct Burial |
| UPC                                   | 781810523605                     |
| UPC 12 Digit                          | 7818105236055                    |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Height inch         | 2.46 in |
| Dimension - L Length Overall mm | 128 mm  |
| Dimension - Length Overall inch | 5.03 in |
| Dimension - Strip Length inch   | 1.125   |
| Dimension - Width inch          | 4.06 in |
| Dimension - Width mm            | 103 mm  |

### Electrical Ratings

|                          |     |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

### Conductor Related

|                                   |  |
|-----------------------------------|--|
| Conductor - AL Str Size Range     | 12 - 350 Str   |
| Conductor - Copper Str Size Range | 12 - 350 Str   |
| Conductor Type                    | <ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul> |

### Certifications and Compliance

|   |     |
|---|-----|
| Certification - CSA Approved            | Yes |
| Certification - ETL                     | No  |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized           | No  |
| Certification - cULus                   | No  |
| Standards - RoHS Compliance Status      | CM  |
| UL Listed                               | Yes |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)