



BIBS3508

by Burndy
Catalog ID: BIBS3508

Prop 65 Notice

MULTI-PORT Single-Sided Entry.

Product Details

General

Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	8
Physical Attribute - Number of Screws	10
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810224076
UPC 12 Digit	7818102240766

Dimensions

Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	195 mm
Dimension - Length Overall inch	7.68 in
Dimension - Width inch	2.32 in
Dimension - Width mm	59 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	10 - 350 Str
Conductor - Copper Str Size Range	10 - 350 Str
Conductor Type	- AL C Str-Size - CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)