



BIBS6008

by Burndy
Catalog ID: BIBS6008

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 8 Port, 1 Sided Entry, 4 AWG-600 kcmil, Al/Cu Rated.

Features: UNITAP Rated For Code Conductor Only, Torque: 375 IN-LB, Wire Entry: Single, Hex Size (key): 3/8 IN, Conductor Size (run - Range): 4 AWG - 600 KCMIL, Number Of Ports: 8, Type Of Insulation: Plastisol, Wire Strip Length: 1-1/8 IN

Product Details

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Hex Key	3/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	8
Physical Attribute - Number of Screws	8
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810224144
UPC 12 Digit	7818102241444

Dimensions

Dimension - Height inch	2.75 in
Dimension - L Length Overall mm	264 mm
Dimension - Length Overall inch	10.41 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Size Range	4 - 600 Str
Conductor - Copper Str Size Range	4 - 600 Str

Conductor Type	• AL C Str-Size • CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)