



## BIBS7503

by Burndy  
Catalog ID: BIBS7503

Prop 65 Notice

MULTI-PORT Single-Sided Entry.

## Product Details

### General

|                                       |               |
|---------------------------------------|---------------|
| Hex Key                               | 3/8           |
| Insulation                            | Y             |
| Insulation Type                       | Plastisol     |
| Material                              | Aluminum      |
| Number Of Ports                       | 3             |
| Physical Attribute - Number of Screws | 3             |
| Physical Attribute - Screw Type       | Allen         |
| Plated                                | N             |
| Plating Type                          | Unplated      |
| Temperature Rating                    | 194           |
| Trade Name                            | UNITAP™       |
| UPC                                   | 781810233061  |
| UPC 12 Digit                          | 7818102330611 |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Height inch         | 3.00 in |
| Dimension - L Length Overall mm | 102 mm  |
| Dimension - Length Overall inch | 4.00 in |
| Dimension - Width inch          | 2.70 in |
| Dimension - Width mm            | 69 mm   |

### Electrical Ratings

|                          |       |
|--------------------------|-------|
| Operating Voltage        | 600 V |
| Rating - Minimum Voltage | 600   |

### Conductor Related

|                                   |  |
|-----------------------------------|--|
| Conductor - AL Str Size Range     | 2 - 750 Str  |
| Conductor - Copper Str Size Range | 2 - 750 Str  |
| Conductor Type                    | <ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul> |

### Certifications and Compliance

|                              |    |
|------------------------------|----|
| Certification - CSA Approved | No |
|------------------------------|----|

|   |              |
|---|--------------|
| Certification - ETL                     | No           |
| Certification - UL Listed Direct Burial | No           |
| Certification - UL Recognized           | No           |
| Certification - cULus                   | No           |
| Industry Standard(s)                    | UL 486A-486B |
| Standards - Industry Standards Met      | UL 486A-486B |
| Standards - RoHS Compliance Status      | CM           |
| UL Listed                               | No           |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)