



BIBS7506

by Burndy
Catalog ID: BIBS7506

Prop 65 Notice

MULTI-PORT Single-Sided Entry.

Product Details

General

Hex Key	3/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	6
Physical Attribute - Number of Screws	6
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810233085
UPC 12 Digit	7818102330855

Dimensions

Dimension - Height inch	3.00 in
Dimension - L Length Overall mm	207 mm
Dimension - Length Overall inch	8.13 in
Dimension - Width inch	2.70 in
Dimension - Width mm	69 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Size Range	2 - 750 Str
Conductor - Copper Str Size Range	2 - 750 Str
Conductor Type	- AL C Str-Size - CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)