



BISR1/OFX

by Burndy
Catalog ID: BISR1/OFX

Prop65

UNITAP, In-Line Splice Reducer, #14-#2 Class B & C, #14-#2 ClassG,H,I,K, DLO, Aluminum.

Features: Clear Plastisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

Product Details

General

Application	Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors
Color Code	Pink
Hex Key	3/16 in
Installation Torque Recommended in-lb	120 in-lb
Insulation	Y
Item Type	3A
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135°C
Trade Name	UNITAP™
Type	BISR,Multi-Port
UPC	621945439979
UPC 12 Digit	6219454399799

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	73.92 mm
Dimension - Length Overall inch	2.91 in
Dimension - Width inch	0.91 in
Dimension - Width mm	23 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - Copper DLO Size Range	14 - 1 Str
-----------------------------------	------------

Conductor - Copper Flex G Size Range	14 - 1 Str
Conductor - Copper Flex H Size Range	14 - 1 Str
Conductor - Copper Flex I Size Range	14 - 1 Str
Conductor - Copper Flex K Size Range	14 - 1 Str
Conductor - Copper Str Size Range	14 -- 1/0 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Fex-Size

Certifications and Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL468A-468B
Standards - Industry Standards Met	UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)