



## BISR2FX

by Burndy  
Catalog ID: BISR2FX

Prop 65 Notice

UNITAP, Tap- Same Sided Entry, #14-#2/0 Class B & C, #14-#1 Class G,H,I,K, DLO, Aluminum.

Features: Clear Plastisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

## Product Details

### General

Application	Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors
Color Code	Brown
Hex Key	5/32 in
Installation Torque Recommended in-lb	100 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135 °C
Trade Name	UNITAP™
Type	BISR,Multi-Port
UPC	621945439962
UPC 12 Digit	6219454399622

### Dimensions

Dimension - Height inch	1.22 in
Dimension - L Length Overall mm	60.45 mm
Dimension - Length Overall inch	2.38 in
Dimension - Width inch	0.75 in
Dimension - Width mm	19.05 mm

### Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

### Conductor Related

Conductor - Copper DLO Size Range	14- 2 Str
Conductor - Copper Flex G Size Range	14 - 2 Str

Conductor - Copper Flex H Size Range	14- 2 Str
Conductor - Copper Flex I Size Range	14- 2 Str
Conductor - Copper Flex K Size Range	14- 2 Str
Conductor - Copper Str Size Range	14- 2 Str
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> <li>• CU C Flex-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)