



BISR350FX

by Burndy
Catalog ID: BISR350FX

Prop 65 Notice

IN-LINE SPLICER/REDUCER.

Product Details

General

Color Code	Red
Hex Key	5/16 in
Installation Torque Recommended in-lb	275 in-lb
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135 °C
Trade Name	UNITAP™
UPC	621945440708
UPC 12 Digit	6219454407088

Dimensions

Dimension - Height inch	2.22 in
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.63 in
Dimension - Width inch	1.34 in
Dimension - Width mm	34 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - Copper DLO Size Range	10 - 250 Str
Conductor - Copper Flex G Size Range	10 - 250 Str
Conductor - Copper Flex H Size Range	10 - 250 Str
Conductor - Copper Flex I Size Range	10 - 250 Str
Conductor - Copper Flex K Size Range	10 - 250 Str
Conductor - Copper Str Size Range	10 -350 Str

Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Flex-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)