



BISR500FX

by Burndy
Catalog ID: BISR500FX

Prop 65 Notice

UNITAP, Tap- Same Sided Entry, #10-250 Class B & C, #10-3/0 Class G,H,I,K, DLO, Aluminum.

Features: Clear Platisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

Product Details

General

Application	Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors
Color Code	Red
Hex Key	3/8 in
Installation Torque Recommended in-lb	375 in-lb
Insulation	Y
Insulation Type	Platisol
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135 °C
Trade Name	UNITAP™
Type	BISR,Multi-Port
UPC	621945440715
UPC 12 Digit	6219454407155

Dimensions

Dimension - Height inch	2.63 in
Dimension - L Length Overall mm	133.35 mm
Dimension - Length Overall inch	5.25 in
Dimension - Width inch	1.63 in
Dimension - Width mm	41.4 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - Copper DLO Size Range	6 - 373 Str
Conductor - Copper Flex G Size Range	6 - 373 Str

Conductor - Copper Flex H Size Range	6 - 373 Str
Conductor - Copper Flex I Size Range	6 - 373 Str
Conductor - Copper Flex K Size Range	6 - 373 Str
Conductor - Copper Str Size Range	6 - 500 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Flex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)