



BITO2/ORK

by Burndy
Catalog ID: BITO2/ORK

Prop 65 Notice

Offset/Double Entry; #14 AWG - 2/0 AWG; 2 Port; Suitable for Hanging on a POS Rack.

Product Details

General

Hex Key	3/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	90°C
Trade Name	UNITAP™
UPC	781810361658
UPC 12 Digit	7818103616588

Dimensions

Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	52.00 mm
Dimension - Length Overall inch	2.03 in
Dimension - Width inch	2.64 in
Dimension - Width mm	67.00 mm

Electrical Ratings

Operating Voltage	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size Range	14 str.- 2/0 str.
Conductor - Copper Str Size Range	14 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	1
Packaging Type	Clamshell

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)