

# BITO250FX

by Burndy  
Catalog ID: BITO250FX

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry  
10-250 Class B, C, and 10-3/0 Class G,H,I,K, DLO



## Product Details

### General

Color Code	Yellow
Hex Key	5/16 in
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440654
UPC 12 Digit	6219454406544

### Dimensions

Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	52.00 mm
Dimension - Length Overall inch	2.03 in
Dimension - Width inch	2.63 in
Dimension - Width mm	66.82 mm

### Electrical Ratings

Operating Voltage	600 V
-------------------	-------

### Conductor Related

Conductor - AL Str Size Range	10 str.- 250 kcmil
Conductor - Copper DLO Size Range	10 str.-3/0 str.
Conductor - Copper Flex G Size Range	10 str.-3/0 str.
Conductor - Copper Flex H Size Range	10 str.-3/0 str.
Conductor - Copper Flex I Size Range	10 str.-3/0 str.
Conductor - Copper Flex K Size Range	10 str.-3/0 str.
Conductor - Copper Str Size Range	10 str.- 250 kcmil

Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li><li>• CU C Flex-Size</li></ul>
----------------	--

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)