



BITO350FX

by Burndy
Catalog ID: BITO350FX

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry
10-350 Class B, C, and 10-250 Class G,H,I,K, DLO

Product Details

General

Color Code	Red
Hex Key	5/16 in
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440661
UPC 12 Digit	6219454406611

Dimensions

Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	56.39 mm
Dimension - Length Overall inch	2.22 in
Dimension - Width inch	2.75 in
Dimension - Width mm	69.85 mm

Electrical Ratings

Operating Voltage	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	10 str.-350 kcmil
Conductor - Copper DLO Size Range	10 str.- 250 kcmil
Conductor - Copper Flex G Size Range	10 str.- 250 kcmil
Conductor - Copper Flex H Size Range	10 str.- 250 kcmil
Conductor - Copper Flex I Size Range	10 str.- 250 kcmil
Conductor - Copper Flex K Size Range	10 str.- 250 kcmil
Conductor - Copper Str Size Range	10 str.-350 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Flex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)