



BITO4FX

by Burndy
Catalog ID: BITO4FX

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry
14-4 Class B, C, and 14-6 Class G,H,I,K, DLO

Product Details

General

Hex Key	1/8 in
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440678
UPC 12 Digit	6219454406788

Dimensions

Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	27.44 mm
Dimension - Length Overall inch	1.08 in
Dimension - Width inch	1.50 in
Dimension - Width mm	38.10 mm

Electrical Ratings

Operating Voltage	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	14 str.- 4 str.
Conductor - Copper DLO Size Range	14 str.-6 str.
Conductor - Copper Flex G Size Range	14 str.-6 str.
Conductor - Copper Flex H Size Range	14 str.-6 str.
Conductor - Copper Flex I Size Range	14 str.-6 str.
Conductor - Copper Flex K Size Range	14 str.-6 str.
Conductor - Copper Str Size Range	14 str.- 4 str.
Conductor Type	- AL C Str-Size - CU C Str-Size - CU C Flex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)