



C22LH1

by Burndy
Catalog ID: C22LH1

Prop 65 Notice

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG -6 AWG, 1-1/4" - 2"
Water Pipe, 1/2" hub

Product Details

General

Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Unplated
UPC	781810142172
UPC 12 Digit	7818101421722

Dimensions

Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.50 in
Dimension - Pad Width inch	1.34 in
Dimension - Width inch	0.69 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG
Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	10 AWG-6 AWG
Conductor - Pipe EMT Size	1 1/4 in;1 1/2 in;2 in
Conductor - Pipe EMT Size Range	1 1/4 in-2 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)