



C61

by Burndy Catalog ID: C61

Prop 65 Notice

Cast Bronze Clamp, Cable to Water Pipe, 6 AWG (Sol.), $1/2^{\prime\prime}$ - 1 $^{\prime\prime}$ Water Pipe.

Features: For Grounding Rigid Conduit Systems, Zinc Plated Screws, Ground Strap: No, Armored Cable: No, Water Pipe Size: 3/8 - 1 IN, Dimension C: 16 IN, Installation Torque: 50 IN-LB For Pipe Clamp And Wire Clamp, Hub Size: 1/2 IN, Height: 27 IN, Width: 1.34 IN, Length: 2.34 IN

Product Details

General

Application	For Grounding Rigid Conduit Systems
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Zinc
Sub Brand	C DIE
Туре	WaterPipe Gounding Connectors
UPC	781810142448
UPC 12 Digit	7818101424488

Dimensions

Dimension - Height inch	2.07 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.34 in
Dimension - Pad Width inch	1.06 in
Dimension - Width inch	1.34 in
Dimension - Width mm	34 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	10 AWG-6 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	8 AWG-6 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor Type	Pipe EMT-SizeCU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)