



C8

by Burndy
Catalog ID: C8

Prop 65 Notice

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 4-1/2" - 6" Water Pipe.

Features: For Connecting Grounding Conductor To Water Pipe Or Copper Tube, Supplied With Zinc Plated Steel Hardware, Water Pipe Size: 4-1/2 - 6 IN, Installation Torque: 50 IN-LB For Pipe And Wire Clamp, Length: 8.34 IN, Cross Flats: 1.88 IN, Width: 1.25 IN, Height: 4.29 IN, Armored Cable: No, Ground Strap: No

Product Details

General

Application	For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube
Material	Bronze Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Trade Name	N
Type	Ground Clamp
UPC	781810142332
UPC 12 Digit	7818101423322

Dimensions

Dimension - Height inch	4.29 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	212 mm
Dimension - Length Overall inch	8.34 in
Dimension - Pad Width inch	1.88 in
Dimension - Thread Size	-
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Pipe EMT Size	4 in

Conductor - Pipe EMT Size Range	4 in
Conductor - Rebar Size Range	N/A

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	N
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)