



CC3Y4/OL12G4

by Burndy
Catalog ID: CC3Y4/OL12G4

Prop 65 Notice

Flexible Rope Lay Copper Braid

Product Details

General

Material	Copper
Plating Type	Tin plated
UPC	621945468634

Dimensions

Dimension - Hole Size inch	0.69 in
Dimension - L Length Overall mm	737 mm
Dimension - Length Overall inch	29 in
Thickness	0.57 in
Weight	8.245 lb

Electrical Ratings

Amperage Rating	1000 A
-----------------	--------

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)