



CCFBGFR

by Burndy
Catalog ID: CCFBGFR

Prop 65 Notice

Flame retardant H-retardant cover, #8-#6 AWG, Green

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece construction
- magnifying lens

Product Details

General

Color	Clear
Color Code	Orange
Connector Type	H-Tap
Material	Polycarbonate
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Temperature Rating	194
UPC	781810438145
UPC 12 Digit	7818104381455

Dimensions

Dimension - Height inch	1.16 in
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.63 in
Dimension - Width inch	0.85 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - Copper Str Size	#8 AWG;#6 AWG
Conductor - Copper Str Size Range	#8 AWG-#6 AWG

Conductor - Max Length	0.65 in
------------------------	---------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)