



CCFDXFR

by Burndy
Catalog ID: CCFDXFR

Prop 65 Notice

Flame retardant H-retardant cover, 250 kcmil, Purple.

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece contruction
- magnifying lens

Two-Piece design with Positive Locking Latch to ensure correct installation,preventing opening after installation and eliminating the need for taping, Mounted Magnifying Lens provides increased visibility of Die Embossment on installed H-Tap Connectors, Made of Polished Clear Polycarbonate material that provides-High visibility for inspection of installed connectors, Flame Retardant UL94 V-O Rated Material-self-extinguishing retardant properties, High impact design, Built in Channels to accommodate and hold Cable ties, Hook & Loop ties, or Waxed Cord, securely in place after installation, Patented highly flexible fingers designed to contour around the conductor, Internal pockets designed to accommodate Identification tags (4 ID tags included),Molded barriers prevent installed H-Tap Connectors from Electrical Flashover, Covers come packaged complete with (2) Cover Halves, (2) Cable Ties and (4) Identification Labels

Product Details

General

Application	Flame Retardant Cover, With Positive Locking Latch to ensure correct installation,preventing opening after installation and eliminating the need for taping
Color	Clear
Color Code	Purple
Connector Type	H-Tap
Fire Resistance	Yes
Material	Polycarbonate
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	FLAME RETARDENT COVER
Temperature Rating	194
Type	CCF-FR,Flame Retardant
UPC	781810452141
UPC 12 Digit	7818104521411

Dimensions

Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6 in
Dimension - Width inch	1.57 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil
Conductor - Max Length	0.95 in

Certifications and Compliance

Certification - 94V0 Rated	Y
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)