



CCFOFR

by Burndy
Catalog ID: CCFOFR

Prop 65 Notice

Clear Polycarbonate H-Tap-Flame Retardant Cover, #2AWG, 600V.

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece construction
- magnifying lens

Two-Piece design with Positive Locking Latch to ensure correct installation, preventing opening after installation and eliminating the need for taping

Product Details

General

Application	Flame Retardant Cover, With Positive Locking Latch to ensure correct installation, preventing opening after installation and eliminating the need for taping
Color	Clear
Color Code	Brown
Connector Type	H-Tap
Fire Resistance	Yes
Material	Polycarbonate
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Type	H-Tap Connector
UPC	781810438176
UPC 12 Digit	7818104381766

Dimensions

Dimension - Height inch	1.44 in
Dimension - L Length Overall mm	112 mm
Dimension - Length Overall inch	4.42 in
Dimension - Width inch	1.21 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - Copper Str Size	#2 AWG
Conductor - Copper Str Size Range	#2 AWG
Conductor - Max Length	0.80 in

Certifications and Compliance

Certification - 94V0 Rated	Y
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)