



CFNFR

by Burndy
Catalog ID: CFNFR

Prop 65 Notice

H-Tap Flame Retardent Cover, 500 kcmil Max Conductor, 1.10" Max Connector Length

- Connector end stops
- Flexible fingers
- snap tight latches
- Hinged one piece construction

Product Details

General

Color	Black
Color Code	Brown
Connector Type	H-Tap
Fire Resistance	Yes
Insulation	Y
Material	Polycarbonate
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	CRIMPIT™
UPC	781810132401
UPC 12 Digit	7818101324011

Dimensions

Dimension - Height inch	2.55 in
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.87 in
Dimension - Width inch	1.98 in
Thickness	0.08 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor - Max Length	1.10 in

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)