



CF-OFR

by Burndy
Catalog ID: CF-OFR

Prop 65 Notice

H Tap Flame Retardent Cover, 2 AWG Max Conductor, 0.80" Max Connector Length.

- Connector end stops
- Flexible fingers
- snap tight latches
- Hinged one piece contruction

Features: One-Piece Design: No Extra Parts Or Hardware Required, Slips Over Connector And Latches Securely Shut: Fast, Easy, Reliable Insulation Of H-Tap Compression, Eliminates Tapping: Economical, Fast, Easy Installation, Flash Barriers: Protects Against Electrical Flashover, CF-FR Flame Retardant Design: Self-Extinguishing Retardant Properties, Minimum 28 Oxygen Index: Self-Extinguishing Retardant Properties, UL 94 V-O Rated: Self-Extinguishing Retardant Properties, H Tap Catalog Number: YH2C2C, Color Code: Brown Connector

Product Details

General

Application	For O, D3, N, And KR Die Size H-Tap Compression Connectors
Color	Black
Color Code	Brown
Connector Type	H-Tap
Fire Resistance	Yes
Insulation	Y
Material	Polycarbonate
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	CF-FR, Flame Retardant
UPC	781810132388
UPC 12 Digit	7818101323888

Dimensions

Dimension - Height inch	1.90 in
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.39 in
Dimension - Width inch	1.49 in
Thickness	0.08 in

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - Copper Str Size	#2 AWG
Conductor - Copper Str Size Range	#2 AWG
Conductor - Max Length	0.80 in

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)