



CFRFR

by Burndy
Catalog ID: CFRFR

Prop 65 Notice

H-Tap Flame Retardent Cover, 750 kcmil /1000 kcmil Max Conductor,
1.30"/1.10" Max Connector Length

- Connector end stops
- Flexible fingers
- snap tight latches
- Hinged one piece construction

Product Details

General

Color	Black
Color Code	Yellow
Connector Type	H-Tap
Fire Resistance	Yes
Insulation	Y
Material	Polycarbonate
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	CRIMPIT™
UPC	781810132425
UPC 12 Digit	7818101324255

Dimensions

Dimension - Height inch	3.58 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.70 in
Dimension - Width inch	2.60 in
Thickness	0.11 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - Copper Str Size	750 kcmil;1000 kcmil
Conductor - Copper Str Size Range	750 kcmil-1000 kcmil

Conductor - Max Length	1.30 in
------------------------	---------

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)