



CL501TNMHWSS

by Burndy
Catalog ID: CL501TNMHWSS

LAY-IN LUG W/SS MOUNTING HDWR DIRECT BURIAL LUG cULus WIRE
RANGE: #14-#4 Cu QUANTITY: 10 PIECES PER BAG

Product Details

General

Material	Copper
Material - Hardware	Stainless Steel
Plated	Y
Plating Type	Tin
Trade Name	QIKLUG™
UPC	781810478769
UPC 12 Digit	7818104787699

Dimensions

Dimension - D inch	0.47 in
Dimension - Height inch	0.85 in
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.13 in
Dimension - N inch	0.19 in
Dimension - Stud Size inch	17/64
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Conductor Related

Conductor - Copper Str Size	14;13;12;11;10;9;8;7;6;5;4
Conductor - Copper Str Size Range	14-4
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	10

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)