

CP34A34A

by Burndy
Catalog ID: CP34A34A

Prop 65 Notice

ACSR,6201,5005: 397.5,477(18-1) CU.& ALUM.: 450,477,500 GROOVE A
GROOVE B



Product Details

General

Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810013021
UPC 12 Digit	7818100130211

Dimensions

Dimension - B Length inch	5 in
Dimension - Height fraction	3 in
Dimension - Height inch	3 in
Dimension - Width fraction	2-1/2 in
Dimension - Width inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	397.5 (26/7) Ibis kcmil-477.0 (18/1) Pelican kcmil
Conductor - AL Str Size A	450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Size A Range	450 kcmil-500 kcmil
Conductor - AL Str Size B	450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Size B Range	450 kcmil-500 kcmil
Conductor - Copper Str Size A	450 kcmil;500 kcmil
Conductor - Copper Str Size A Range	450 kcmil-500 kcmil
Conductor - Copper Str Size B	450 kcmil;500 kcmil
Conductor - Copper Str Size B Range	450 kcmil-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)