



CT120500SSBC0

by Burndy

Catalog ID: CT120500SSBC0

Nylon Stainless Steel BARB Cable Ties, 17.72 IN L, .39 IN W, Tensile Strength: 120 Lbs, Installation Tool: MK9, TWT2.

- Stainless Steel Barb Tie
- Nylon 6/6 Standard, Self-locking stainless steel barb, Maximum strength and adjustability for versatility

Product Details

General

Application	For use with self-locking stainless steel barb
Color	Black
Material	Nylon 6/6
Rating - Minimum Tensile Strength N	124
Rating - Minimum Tensile Strength lbs	120 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565087

Dimensions

Dimension - Bundle Diameter Max inch	4.92
Dimension - L Length Overall mm	450 mm
Dimension - Length Overall inch	17.72 in
Dimension - Width inch	0.39 in
Dimension - Width mm	10 mm

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2000 EA
-----------------	---------

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)